



Technical Datasheet

Plasma Display Stand

Specifications:

Size: 33 x 16 x 17cm

Shipping size :
23 x 23 x 44cm

Unit weight : 1.4kg

Shipping weight : 2.2kg

Packaging type : Box

Base Height :
5 x 16 x 17cm

Illuminated area :
26.5cm x 14cm

Voltage : 220-240V

Power connector :
13A mains plug

Amps drawn : 1 amp

Suggested for set up :
1 person

Duration of effect :
Can be used continually
for up to 10 hours

The plasma display stand uses a combination of plasma lightning effects and LED lighting to display your choice of item; available in three colours

How to set up and use a plasma display stand

1. Carefully remove the plasma display stand from the transport box and set it onto a stable, flat surface.
2. Prepare your presentation surface and make sure it is stable and free from surrounding metal objects. Position the plasma display stand and plug in the power lead.
3. Switch on and select between normal operation and audio response using the switch on the back of the unit.
4. The glass panel can be touched, but be aware that this may result in some heat transfer or a buzzing sensation.
5. When unplugged, wait 60 seconds before handling wires or plugs.

Hints and tips

- The unit has two modes; continuous or audio response
- Make sure the unit is switched off and unplugged before cleaning.
- Don't touch the panel with metal objects as this may cause an arc to form, and will damage the glass and seals.
- Avoid setting up near metal objects or areas of high humidity.
- Only use the plasma display stand indoors.
- The plasma display stand may cause electrical interference with nearby items
- Ensure all local metalwork is earthed
- Don't allow to overheat



Plasma Display Stand



Power connection



Audio response on/off switch



Touch effect



Display stand in operation